

Specificatielijst GM70

| | GM70 |
|-----------------------------|----------------------------------|
| Afmetingen: | |
| Lengte (mm) | 65 |
| Breedte (mm) | 120 |
| Diepte (mm) | 22 |
| Gewicht (gram) | 140 inclusief batterijen |
| LCD-scherm: | |
| LCD-scherm | |
| Voeding: | |
| Voeding | 2 AA cellen |
| Levensduur batterij: | |
| Levensduur batterij | 16 uur |
| Demping: | |
| Demping | > 15dB (51 kHz tot 3,072 MHz) |
| Dynamische bereik: | |
| Dynamische bereik | 0 tot -11dB of 0 tot -43dB |
| In/uitgangen: | |
| In/uitgangen | 2 x BNC connectors |
| Geleider: | |
| Geleider | Typische 3 kV |
| Impedantie: | |
| Impedantie | 75 Ohm, 120 Ohm of HI Z |
| Snelheid: | |
| E1 | 2.048 MB |
| Asynchroon | |
| Synchroon | |
| Toont op display: | |
| Bit errors | |
| Bit error rate | |
| Karakter errors | |
| Totale testduur in secondes | |
| Errored secondes | |
| Ontvangen karakters | |
| Severely errored secondes | |
| Degraded Minutes | |
| Beschikbaar | |
| Niet beschikbaar | |
| Verzend frequentie | |
| Onvangst frequentie | |
| Clear to send vertraging | |
| Ontvangen bits | |
| Leds: | |
| Pattern Lock | • |
| Pattern Recovered | |
| Transmit Data | |
| Received Data | |
| Request To Send (C) | |
| Clear To Send | |
| Data Set Ready | |
| Carrier Detect (I) | |
| Data Terminal Ready | |
| Transmit Clock | |
| Receive Clocks (S) | |
| External Transmit Clock | |
| Frame Lock | |
| All 1s | • |
| All 0s | |
| CRC Error | • |
| BiPolar Violation | • |
| Distant Multiframe Alarm | • |
| Receive Remote Alarm | • |

| | GM70 |
|---|---|
| CAS errors | • |
| G.704 | |
| PRBS | |
| LOS | |
| LFA | |
| RA1 | |
| DCRC | |
| FAS | Frame Synch/ Errors/ Error rate < 103 |
| PRP | Pattern Synch/ Errors/ Error rate < 103 |
| Line Signal HDB3 signal detector | • |
| Rdy/Synch Test pattern Synch/ test pattern output | • |
| Low battery | • |
| Toetsen en schakelaars: | |
| Reset display | |
| Configuratie | |
| Change | |
| Mode | |
| Loop | |
| Reset | • |
| Power on/off | • |
| Input | Hi= -43dB Lo= - 11 dB |
| Impedantie | • |
| Monitor mode | BERT master of slave |
| Inject errors | • |
| Latch/momentary | • |
| History | |
| Scroll | |
| Select | |
| Patronen: | |
| PRP15 ($2^{15} - 1$) | • |
| 2^6 (63) | |
| 2^9 (511) | |
| 2^{11} (2,047) | |
| Binary | |
| Fox test | |
| Marks | |
| Spaces | |
| 2^{15} (32,767) | |
| QRSS | |
| 2^{20} (1,048,575) | |
| 2^{23} (8,388,607) | |
| 1 of 8 | |
| 3 of 24 | |
| Loops: | |
| Self-Test | |
| V.54 | |
| Interfaces: | |
| RS232 | |
| RS449 | |
| RS530 | |
| V.35 | |
| X.21 | |
| CCITT G.703 | |
| CCITT G.704 | |
| HDB3 Coding | |
| Full/Fractional | |
| Goedkeuring: | |
| CE goedgekeurd | • |
| Leveringsomvang: | |
| De tester | • |
| AC transformator | |
| Koffer | • |
| Serial remote control | |
| Nederlandstalige gebruiksaanwijzing | • |

| | |
|---|-------------|
| | GM70 |
| Optioneel: | |
| Uitvoering met lader en ingebouwde accu | |
| MB04 en MB15 in koffer | |